



# KSU26, Split Bolt Connector with Spacer. Tin Plated

By Burndy  
Catalog # [KSU26](#)

Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors, 1.90 IN L.



## Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

## General

Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	385
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810036600
UPC 12 Digit	7818100366000

## Dimensions

Dimension - Cross Flats inch	1.04 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.95
Dimension - Width inch	0.79 in
Dimension - Width mm	20 mm
Width	0.79 in

## Conductor Related

Conductor - AAAC 5005 Run	123.3 (7) kcmil
Conductor - AAAC 5005 Run Range	123.3 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 6201 Run	123.3 (7) kcmil
Conductor - AAAC 6201 Run Range	123.3 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - ACSR Str Run	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Run Range	1 AWG - 1/0 AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	6 AWG - 1/0 AWG
Conductor - AL Str Run	2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	2 AWG - 2/0 AWG
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	8 AWG - 2/0 AWG
Conductor - Copper Solid Run	22
Conductor - Copper Solid Run Range	22
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	2 AWG - 2/0 AWG
Conductor - Copper Str Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	8 AWG - 2/0 AWG
Conductor - Galvanized Steel	7/16 (7) in

Conductor - Galvanized Steel	7/16 (7) in
Str Size	
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Run</li> <li>• AAAC C 5005-Run</li> <li>• AAAC C 6201-Run</li> <li>• ACSR C Str-Run</li> <li>• CU C Solid-Tap</li> <li>• CU C Str-Tap</li> <li>• AL C Str-Tap</li> <li>• AAAC C 5005-Tap</li> <li>• AAAC C 6201-Tap</li> <li>• ACSR C Str-Tap</li> <li>• GAL Steel C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5800

### Product Assets

- [3D Models - KSU26\\_MODEL-PDF](#)
- [3D Models - KSU26\\_MODEL-IGES](#)
- [3D Models - KSU26\\_MODEL-STEP](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..041343-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-KSU26-SPEC-EN | REV 8/2023