

Eaton KTK-20

Catalog Number: KTK-20

Eaton Bussmann series KTK fuse, Control circuits, Lighting circuit protection, Meter circuits, 20 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, Melamine tube|Nickel-plated bronze endcap, 600 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series KTK fuse	KTK-20
UPC	Product Length/Depth
051712420204	1.5 in
Product Height	Product Width
0.41 in	0.41 in
Product Weight	Warranty
0.18 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical rating

Amperage Rating

20 A

Interrupt rating

100 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Material

Nickel-plated bronze endcap

Melamine tube

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Small footprint

Resources

Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - KTK-20](#)

Technical data sheets

[KTK-20-LIMITRON FAST ACTING FUSE](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)