



KTKR10 10A 600V Fa Class CC Fuse

Bussmann Fuses

Catalog Number	KTFR10
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, Class CC Fuse, Ferrule End X Ferrule End Connection, 10 A, 600 V Ac, Melamine Tube Material, 0.41 In Diameter, 1.5 In Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	10
connection	Ferrule end x ferrule endFerrule
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
media	Yes

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	10A 600V FA CLASS CC FUSE
extra long description	BUSS KTK-R-10 CLASS CC FAST ACTING
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Special Features	Rejection Style

Manufacturer Information

Brand	Eaton
GTIN	00051712420686
UPC	051712420686

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	10
Weight Per each	0.02



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln
79109-3210, TX Amarillo
Phone: 806-220-0404
Fax: 806-220-0811

Uses, Certifications, and Standards

standard

UL Listed, CSA Certified, CE Marked, RoHS Compliant