

Eaton Bussmann series KTK-R fuse

KTK-R-10

UPC:051712420686

Dimensions:

- **Height:** .41 IN
- **Length:** 1.5 IN
- **Width:** .41 IN

Weight:.18 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Current-limiting, fast acting
- **Special Features:** Rejection Style
- **Application:** Specialized circuits and industrial control
- **Voltage Rating:** 600V
- **Amperage Rating:** 10A
- **Interrupt Rating:** 200 kAIC
- **Class:** Class CC
- **Connection:** Ferrule end X ferrule end
- **Material Type:** Melamine tube
- **Packaging Type:** Standard
- **Diameter:** .40625 IN
- **Fuse Indicator:** Non Indicating

Supporting documents:

- [Product Catalog](#)
- [CLASS CC FAST ACTING FUSE CLASS CC](#)
- [Product Datasheet](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant



