# Eaton KTK-R-10

## Catalog Number: KTK-R-10

Eaton Bussmann series KTK-R fuse, Rejection style, Specialized circuits and industrial control, 10 A, Class CC, Non-indicating, Ferrule end x ferrule end, 200 kAIC, Melamine tube, Standard, 600 V



### General specifications

**Product Name** 

Eaton Bussmann series KTK-R fuse

**UPC** 

051712420686

**Product Height** 

0.41 in

**Product Weight** 

0.18 lb

Compliances

CE Marked

**RoHS Compliant** 

Catalog Number

KTK-R-10

Product Length/Depth

1.5 in

**Product Width** 

0.41 in

Warranty

Not Applicable



#### **Product specifications**

Fuse indicator

Non-indicating

Special features

Rejection style

Interrupt rating

200 kAIC

Type

LIMITRON Fast-acting fuse

Connection

Ferrule end x ferrule end

Class

Class CC

Material

Melamine tube

Voltage rating

600 V

Application

Specialized circuits and industrial control

**Amperage Rating** 

10 A

Packaging type

Standard

#### Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - KTK-R-10

Technical data sheets

KTK-R-10~CLASS CC FAST ACTING FUSE CLASS CC

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia