



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2818 NE Independence Avenue
64064-0000, MO Lee's Summit
Phone: 816-924-7000
Fax: 816-931-2918



KTLED9A190840UV 9W Led A19 40K 800LM 120-277V Non-Dim

Keystone Technologies

Catalog Number	KTLED9A190840UV
Manufacturer	Keystone Technologies
Description	A19 Omni-Directional Bulb, 60W Equivalent, E26 Medium Base, 4000K, 80 Cri, Universal Voltage 120-277V
Weight per unit	0.0026 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	230
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	A19
lumens	840
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	9
Wire Type	N/A

Material, Color, and Finish

Base Type	E26
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

Descriptions

Description	9W LED A19 40K 800LM 120-277V NON-DIM
extra long description	Key KT-LED9A19-O-840-UV A19 Omni-Di
Long Description	A19 Omni-Directional Bulb, 60W Equivalent, E26 Medium Base, 4000K, 80 CRI, Universal Voltage 120-277V
Product Type	A19 Omni-Directional Bulb, 60W Equivalent, E26 Medium Base,

Manufacturer Information

Brand	Keystone
GTIN	00843654134642
Manufacturers Part Number	KT-LED9A19-O-840-UV
UPC	843654134642



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2818 NE Independence Avenue
64064-0000, MO Lee's Summit
Phone: 816-924-7000
Fax: 816-931-2918

Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Packaging

Carton 1

Package 60

Weight Per each 0.0026

Uses, Certifications, and Standards

Energy Star Y