




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5300 Bandera Road
78238-0000, TX Leon Valley
Phone: 210-522-0146
Fax: 210-522-0732



KTTFLED100PS850 60/80/100W Led Temp Light 50K 7200-12000LM *Keystone Technologies*

Catalog Number	KTTFLED100PS850
Manufacturer	Keystone Technologies
Description	Led Temporary Jobsite Fixture. Power Selectable 60/80/100W, 6, 800-10, 000 Lumen, 5000K. Diffused Lens. Includes 6FT Power Cord, Mounting Hook, and Safety Cage, Linkable Design
Weight per unit	8.6 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	360
Circuit Type	N/A
Input Voltage	120V
ip rating	IP64
Nominal Length	N/A
Nominal Size	1 ft Round
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	N/A
Wire Type	N/A

Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	Gray

Descriptions

Description	60/80/100W LED TEMP LIGHT 50K 7200-12000LM
extra long description	Key KT-TFLED100PS-850 LED Temporary
Long Description	LED Temporary Jobsite Fixture. Power Selectable 60/80/100W, 6,800-10,000 lumen, 5000K. Diffused Lens. Includes 6ft Power Cord, Mounting Hook, and Safety Cage, Linkable Design
Product Type	Led Temporary Jobsite Fixture. Power Selectable 60/80/100W,



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5300 Bandera Road
78238-0000, TX Leon Valley
Phone: 210-522-0146
Fax: 210-522-0732

Manufacturer Information

Brand	Keystone
GTIN	00843654133980
Manufacturers Part Number	KT-TFLED100PS-850
UPC	843654133980

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
----------------------	---

Packaging

Carton	1
Package	4
Weight Per each	8.6

Uses, Certifications, and Standards

Energy Star	N
-------------	---