



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

L10.5T848G830DX2 10.5W Led T8 48" 30K Singl/DBL Ended 1700LM Glass *Keystone Technologies*



Catalog Number	L10.5T848G830DX2
Manufacturer	Keystone Technologies
Description	10.5W Led T8 Tube, Glass Construction, 120-277V Input, 4 FT., 3000K, Direct Drive, Single or Double Ended
Weight per unit	0.7000 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	T8
lumens	1650
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	10.5
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	3000
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	10.5W LED T8 48" 30K SINGL/DBL ENDED 1700LM GLASS
extra long description	Key KT-LED10.5T8-48G-830-DX2 /G2-CP
Long Description	10.5W LED T8 Tube, Glass Construction, 120-277V Input, 4 ft., 3000K, Direct Drive, Single or Double Ended
Product Type	10.5W Led T8 Tube, Glass Construction, 120-277V Input, 4 FT.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654132891
Manufacturers Part Number	KT-LED10.5T8-48G-830-DX2 /G2-C
UPC	843654132891

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.7

Uses, Certifications, and Standards

Energy Star	N
-------------	---