legrand[®] designed to be better.

20 Amp NEMA L1020 Single Receptacle

L1020R



Turnlok Receptacle 3wire 20amp 125/250v



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 #10 AWG.

features & benefits

specifications

General Info

Type: Single, Receptacles Number Of Wires: 3

Listing Agencies/Third Party Information

CSA Listing Info: No CUL Listing No: No cULus: No cURus: No Federal Spec: Yes

L1020R

Fed Spec Number: WC596 UL Listing No: 498 UL Standard: Yes UN SPS C: 39121403 UR: No

Dimensions

Depth U S: 1.19" Height U S: 3.28" Width U S: 1.61"

Technical Information

Amps: 20 Amp NEMA Configuration Number: L1020 Volts: 125/250V Volts A C: 125/250

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant