



KT-LED12HID-E26-830-D HID REPLACEMENT LED LAMP

DESCRIPTION

12W HID Replacement LED Lamp | 3000K | > 80 CRI | IP64 Rated

LAMP TYPE: HID Replacement LED

BASE TYPE: E26 (Medium)

WATTAGE: 12W

COLOR TEMPERATURE: 3000K

METAL HALIDE EQUIVALENT: 50W

COLOR RENDERING INDEX (CRI): >80

WARRANTY: 5 Years

PRODUCT FEATURES

- Replacement for conventional metal halide lamp
- Non-dimmable; do not dim
- 50,000 + hour lifetime
- Environmentally friendly: No mercury used
- Instant startup
- UL listed

• Operating temperature: -40°C/-40°F to 60°C/140°F

- Integral driver, eliminates the need for external driver or ballast; includes 4kV surge protection
- IP64 rated; integrated heat sink quickly dissipates heat and guides water intrusion out of the lamp
- Suitable for use in fully enclosed fixture

Lamp does not meet CEC T20 requirements. Not to be sold or offered for sale in California, except when sold wholesale in California for final retail sale outside the state.

OPERATING SPECIFICATIONS

ELECTRICAL CHARACTERISTICS


Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	12W	>0.9	0.10A @ 120V 0.04A @ 277V

PHOTOMETRIC CHARACTERISTICS


Color Temperature (CCT)	3000K
Luminous Flux	1620 lm
Color Rendering Index (CRI)	>80
Efficacy	135 lm/W
Visible Light Area	360°

RATED LIFE

	L70 (Hours)	50,000



LUX DISTANCE CURVE










KT-LED12HID-E26-830-D HID REPLACEMENT LED LAMP

WIRING DIAGRAM

STEP 1

Disconnect power. Disconnect and remove existing ballast, capacitor, and/or ignitor (where applicable) from fixture.





Rewire for line voltage to the lamp socket.





STEP 3

Install new LED replacement lamp. Ensure lamp is operating properly when power is turned on.



PHYSICAL CHARACTERISTICS





LAMP DIMENSIONS

A (Illuminated Length)	1.65"
B (Body Length)	4.92"
C (Diameter)	2.36"

BASE TYPE: E26 (Medium)

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED12HID-E26-830-D-DP	Distributor Pack (Individual Cartons)	16	Quick Ship

L OAC

120-277

NÔ

CATALOG NUMBER BREAKDOWN

