



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104



L12T836GC840DX2 12W Led T8 36" 40K Line DBL/SNGL Ended 1450LM *Keystone Technologies*

Catalog Number	L12T836GC840DX2
Manufacturer	Keystone Technologies
Description	12W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 3, 4000K, Direct Drive, Single or Double Ended
Weight per unit	0.5600 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1500
Nominal Length	36 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	12
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Description	12W LED T8 36" 40K LINE DBL/SNGL ENDED 1450LM
extra long description	Key KT-LED12T8-36GC-840-DX2-CP 12W
Long Description	12W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 3, 4000K, DIRECT DRIVE, SINGLE OR DOUBLE ENDED
Product Type	12W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input,



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104

Manufacturer Information

Brand	Keystone
GTIN	00890949019221
Manufacturers Part Number	KT-LED12T8-36GC-840-DX2-CP
UPC	890949019221

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.56

Uses, Certifications, and Standards

Energy Star	Y
-------------	---