



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L14.5T848G850DX2 *Please Use Catalog L145T848G850DX2G***** *Keystone Technologies*

Catalog Number	L14.5T848G850DX2
Manufacturer	Keystone Technologies
Description	14.5W Led T8 Tube, Glass Contruction, 4FT, 5000K, 120-277V Input, 25 PCS Carton, Direct Drive Single or Double Ended.
Weight per unit	0.6600 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1950
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	14.5
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Construction	N/A
Description	***PLEASE USE CATALOG L145T848G850DX2G***
extra long description	Key KT-LED14.5T8-48G-850-DX2-CP 14.
Long Description	14.5W LED T8 TUBE, GLASS CONTRUCTION, 4FT, 5000K, 120-277V INPUT, 25 PCS CARTON, DIRECT DRIVE SINGLE OR DOUBLE ENDED.
Product Type	14.5W, 1900 Lumen, 240' Beam Angle, Ballast Bypass, DLC 4.0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654120997
Manufacturers Part Number	KT-LED14.5T8-48G-850-DX2-CP
UPC	843654120997

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Availability

Status	Inactive
--------	----------

Packaging

Carton	25
Weight Per each	0.66

Uses, Certifications, and Standards

Energy Star	Y
-------------	---