

Eaton L1420P

Catalog Number: L1420P

Eaton locking plug, #16-12 AWG, 20A, Industrial, 125/250V, Back wiring, Black, white, Ultra grip, L14-20, Three-pole, Four-wire, Nylon



General specifications

Product Name	Catalog Number
Eaton Arrow Hart standard locking plug	L1420P
UPC	Product Length/Depth
032664391804	1.84 in
Product Height	Product Width
3.2 in	1.84 in
Product Weight	Compliances
0.19 lb	RoHS Compliant
Certifications	
UL Listed	
NOM	
CSA certified	
cULus Listed	

Product specifications

Special features

Severe duty locking connector

Color

White

Black

Face/body material

Thermoplastic

Wiring method

Back

Material

Thermoplastic

Allowable wire size

#16-12 AWG

Amperage Rating

20A

Number Of Poles

Three-pole

Contact material

Brass

Type

Locking plug

Device grade

Commercial

NEMA configuration

L14-20

Design type

Standard locking plug

Number of wires

Grounding

4

Operating temperature

-20 to 60 °C (-4 to 140 °F)

Voltage rating

125/250 V

Cord diameter

0.25-0.69 in (6.4 mm-17.5 mm)

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - L1420P](#)

Application

Industrial

Torque rating

15 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)