



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1420R 20A 4W 125/250V TL Rec *Pass & Seymour/Legrand*

Catalog Number	L1420R
Manufacturer	Pass & Seymour/Legrand
Description	Turnlock Single Receptacle, 20 A, 125/250 V Ac, 2 Poles, 4 Wires, #14 to #10 Awg Compatible Wire Size, Back Wire Connection, Receptacle, 2.3 In Length, Nylon Material, Black/White, Impact Resistant, 0.2400 LB
Weight per unit	0.2396 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20 A
Poles	2 in
Wire Size	4 in

Dimensions and Weight

Size	2.3 in
------	--------

Descriptions

Description	20A 4W 125/250V TL REC
-------------	------------------------

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007142051
sub brand	Pass & Seymour
UPC	785007142051

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlock Single Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.2396

Uses, Certifications, and Standards

Mounting	Receptacle
standard	UL 498



20 AMP NEMA L1420 SINGLE RECEPTACLE

L1420R | [Pass & Seymour](#)

FEATURES & BENEFITS

Turnlok Single Receptacle 4wire 20amp 125/250v



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Single Receptacles
Number Of Wires: 4

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.19"
Height (US): 3.28"

Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L1420

Volts: 125/250V

Volts (AC): 125/250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

