



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1520P 20A 4W 250V 3PH TL Plug

Pass & Seymour/Legrand

Catalog Number	L1520P
Manufacturer	Pass & Seymour/Legrand
Description	Locking Device Turnlock Plug, 20 A, 250 V Ac, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 2.20 In;0.225 to 1.150 In (Cord) Diameter, Plug Mount, 3.75 In Length, #18 to #8 Awg Wire Size, Impact and Corrosion Resistant, 0.35 LB
Weight per unit	0.3460 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20 A
Poles	2 in

Dimensions and Weight

Size	3.8 in
------	--------

Descriptions

Description	20A 4W 250V 3PH TL PLUG
-------------	-------------------------

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007152043
sub brand	Pass & Seymour
UPC	785007152043

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlock Plug

Packaging

Carton	10
Weight Per each	0.346

Uses, Certifications, and Standards

Mounting	Plug
standard	UL 498

20 AMP NEMA PLUG L1520 - BLACK BACK, WHITE FRONT BODY

L1520P | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Plug 4wire 20amp 3phase 250v



PRODUCT
ENVIRONMENTAL PROFILE

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

SPECIFICATIONS

GENERAL INFO

Color: Black, White

Type: Plug

Number Of Wires: 4

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Diameter (US): 2.20"

Length (US): 3.75"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L1520

Volts: 250V

Volts (AC): 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

