



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L15T848GC865DX2 15W Led T8 48" 65K Line DBL/SNGL Ended *Keystone Technologies*

Catalog Number	L15T848GC865DX2
Manufacturer	Keystone Technologies
Description	Linear Fluorescent Led Lamp, Linear, Single/Double Ended, Instant Start Type; 47.5 Inch; UI (Canada and Us), UI, NSF/Ansi, Etl, DLC Approval; Food Equipment Application; 120 to 277 Volt Ac Voltage Rating; 1.1 Inch Diameter
Weight per unit	0.6600 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Beam Spread Angle	240 Degree
Current Rating	0.16 Amp at 120 Volt AC, 0.07 Amp at 277 Volt AC
Glass Finish	FROSTED
Intensity	1900 LUMEN
Item	LED Tube
Voltage Rating	120 to 277 Volt AC
Wattage	15 Watt

Material, Color, and Finish

Base Type	G13 Medium 2-Pin
Color Rendering Index	83
Color Temperature in Kelvin	6500

Dimensions and Weight

Diameter	1.1 Inch
Length	47.5 Inch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	RoHS Compliant; Shatter Proof Coated Glass; Efficacy 127 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F
Commodity Description	Led Linear Fluorescent Straight, U-Shape & Circular Lamps
Description	15W LED T8 48" 65K LINE DBL/SNGL ENDED
extra long description	LINEAR, SINGLE/DOUBLE ENDED, INSTANT START TYPE; 47.5 INCH; UL (CANADA AND US), UL, NSF/ANSI, ETL, DLC APPROVAL; FOOD EQUIPMENT APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 1.1 INCH DIAMETER; 0.16 AMP AT 120 VOLT AC, 0.07 AMP AT 277 VOLT AC CURRENT RATING; 15 WATT WATTAGE; LED TUBE; G13 MEDIUM 2-PIN BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 1900 LUMEN INTENSITY; 6500; 83 COLOR RENDERING INDEX; FROSTED GLASS FINISH; 240 DEGREE BEAM SPREAD ANGLE; DIRECTDRIVE DX2 BRAND; ROHS COMPLIANT; SHATTER P
Long Description	LINEAR FLUORESCENT LED LAMP, LINEAR, SINGLE/DOUBLE ENDED, INSTANT START TYPE; 47.5 INCH; UL (CANADA AND US), UL, NSF/ANSI, ETL, DLC APPROVAL; FOOD EQUIPMENT APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 1.1 INCH DIAMETER
Product Type	Linear Fluorescent Led Lamp

Manufacturer Information

Brand	Keystone Technologies
GTIN	00890949016350
Manufacturers Part Number	KT-LED15T8-48GC-865-DX2
Model	800
UPC	890949016350

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Linear, Single/Double Ended, Instant Start

Packaging

Carton	1
Package	25
Weight Per each	0.66

Uses, Certifications, and Standards

Application	Food Equipment
Approval	UL (Canada and US), UL, NSF/ANSI, ETL, DLC