

20 Amp NEMA L1620 Single Receptacle

L1620R



Turnlok Single Receptacle 4wire 20amp
3phase 480v



features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

specifications

General Info

Type: Single, Receptacles
Number Of Wires: 4

Listing Agencies/Third Party Information

CSA Standard: Yes
cULus: No
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: 498

UL Standard: Yes
UN SPS C: 39121403

Dimensions

Depth U S: 1.19"
Length U S: 3.28"
Width U S: 1.61"

Technical Information

Amps: 20 Amp
NEMA Configuration Number: L1620
Volts: 480V
Volts A C: 480

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant