

Specifications

Eaton L1630PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 480V, Back, Yellow, Steel, Watertight, L16-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67

General specifications

PRODUCT NAME	Eaton Arrow Hart watertight locking plug
CATALOG NUMBER	L1630PW
UPC	040893642123
PRODUCT LENGTH/DEPTH	6.75 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	0.81 lb
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Watertight locking plug



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	30A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L16-30
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	480 V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight locking plug

Environmental Specifications

ENVIRONMENTAL RESISTANCE	Watertight
--------------------------	------------

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Steel

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - L1630PW Arrow Hart watertight locking plugs, connectors and receptacles spec sheet
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

