

# 30 Amp NEMA L1630 Single Receptacle

L1630R



Turnlok Single Receptacle 4wire 30amp 3phase 480v



## features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 #10 AWG.

# specifications

#### **General Info**

Type: Single, Receptacles Number Of Wires: 4

#### **Listing Agencies/Third Party Information**

CSA Standard: Yes Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: 498 UL Standard: Yes UN SPS C: 39121403

#### **Dimensions**

Depth U S: 1.28" Height U S: 3.28" Width U S: 1.61"

#### **Technical Information**

Amps: 30 Amp

NEMA Configuration Number: L1630

Volts: 480V Volts A C: 480

## **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant