FEATURES:


- Material: Tin Plated CU UL listed for U.S. & Canada.
- Wire connector rated for 35Kv max.
 Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).


 Dimensions are for reference only.


LN Series: L1N

PROGRAM: SOLIDWORKS
UPDATED: 4/2022

SALES REV: A
SIZE: B (11x17)







+			COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)									
			NSI			GREENLEE	ILSCO	BURNDY	T&B	HUS	SKIE	
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES	ILC-12/ILC-15 SERIES	Y-35, Y750, PAT 750	TBM-15, TBM-14M	FM EP510C	
#1AWG	1-3/16"	GREEN	#1AWG-#6AWG	KC12-1 (2)	CD5 (4)	HT41AX (4)	KC12-1 (2)	ILD-4 (4) KC12-1(2)	U1CRT-1 (2)	15513-CK (4)	HT41AX (4)	CD5 (4)

