

# 20 Amp NEMA Connector L2120 - Black Back, White Front Body

L2120C



Turnlok Connector 5wire 20amp 3phase 120/208v



# features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the iob site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

# specifications

#### **General Info**

Color: Black, White Type: Connector

Number Of Wires: 5

## **Listing Agencies/Third Party Information**

CSA Standard: Yes Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: 498 UL Standard: Yes UN SPS C: 39121403

### **Dimensions**

Diameter U S: 2.20" Length U S: 3.33"

#### **Technical Information**

Amps: 20 Amp

NEMA Configuration Number: L2120

Volts: 120/208V Volts A C: 120/208

## **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant