



Pass and Seymour
20A NEMA Plug L2120 - Black Back, White Front Body
Part No. L2120P

Turnlok® Plug 5-Wire 20A 3-Phase 120/208V



Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007212044	Country Of Origin	Mexico
Features	Locking	Application Sector	Industrial
Standard	UL 498, FDSPEC	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	2.2 in	Product Length US	2.57 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	146159	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Connector Style	Locking	Flanged	No
Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	5
Amperage	20 A	Number of Poles	3-Way
Indoor/Outdoor	Indoor	NEMA Configuration Code	L21-20P
Number of Phases	3	Voltage	125/208 V