



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L2120R 20A 5W 120/208V 3PH TL Receptacle

Pass & Seymour/Legrand

Catalog Number	L2120R
Manufacturer	Pass & Seymour/Legrand
Description	
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20 A
Material	NYLON
Number of Wires	3 in
Poles	2 in
Voltage Rating	120/208 VAC
Wire Size	4 in

Material, Color, and Finish

Color	BLACK
-------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 5W 120/208V 3PH TL RECEPTACLE
Product Type	Turnlok SGL Rec 5W 20A 4P 120/208V
Special Features	Locking Device, impact resistant

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007212051
Manufacturers Part Number	L2120-R
sub brand	Pass & Seymour
UPC	785007212051

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlock Single Receptacle

Packaging

Carton	10
Package	1
Weight Per each	0.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Industrial Spec Grade
Mounting	Receptacle
nema rating	L21-20R
standard	UL 498

20 AMP NEMA L2120 SINGLE RECEPTACLE

L2120R | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Single Receptacle 5wire 20amp 3phase 120/208v



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Single Receptacles
Number Of Wires: 5

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.19"
Height (US): 3.28"

Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L2120

Volts: 120/208V

Volts (AC): 120/208

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

