**FEATURES:** 

Material: Tin Plated CU

UL listed for U.S. & Canada.

- 3. 4. Wire connector rated for 35Kv max.
  Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).
- Dimensions are for referene only.


L Series: L214


**POLARIS** 


PROGRAM: SOLIDWORKS **UPDATED:** 4/2022

SALES REV: A

**SIZE:** B (11x17)







| +         |              |           | COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS) |              |         |            |             |                      |           |                                     |           |            |         |
|-----------|--------------|-----------|---|--------------|---------|------------|-------------|----------------------|-----------|-------------------------------------|-----------|------------|---------|
|           |              |           | NSI   |              |         | GREENLEE   | ILSCO       |                      | BURNDY    | T&B                                 | HUSKIE    |            |         |
| WIRE SIZE | STRIP LENGTH | DIE COLOR | EXPANDED WIRE RANGE<br>W/N12ID                                | N1240 SERIES | NSI-12  | NSI-12     | 1240 SERIES | ILC-12/ILC-15 SERIES |           | Y-35, Y750, PAT 750 TBM-15, TBM-14M |           | EP510C     |         |
| #2AWG     | 1-3/16"      | BROWN     | #2AWG-#6AWG   | KC12-2 (2)   | CD4 (4) | HT41AW (4) | KC12-2 (2)  | ILD-4 (4)            | KC12-2(2) | U2CRT (2)                           | 15528 (4) | HT41AW (4) | CD4 (4) |

