


- **FEATURES:** 1. Material: Tin Plated CU 2. UL listed for U.S. & Canada.
- 2. 3. 4.
- Wire connector rated for 35Kv max. Class B/C compressed, concentric, and compact copper conductor only.
- Expanded wire range when installed with dieless NSi compression tool (N12ID). Dimensions are for referene only. 5.
- 6.

L Series: L3038









╡╶╋			COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)										
			NSI				GREENLEE	ILSCO		BURNDY	T&B	HUSKIE	
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES	ILC-12/ILC-15 SERIES		Y-35, Y750, PAT 750	TBM-15, TBM-14M	EP510C	
3/0AWG	1-7/16"	ORANGE	3/0AWG-#2AWG	KC12-3/0 (2)	CD10 (4)	HT41BA (4)	KC12-3/0 (2)	ILD-9 (4)	KC12-3/0 (2)	U27RT (2)	15530 (4)	HT41BA (4)	CD10 (4)
	nsiindustries.com/contactus 800.321.5847 📦												

	SOLIDWORKS
UPDATED:	4/2022
SALES REV:	
SIZE:	B (11x17)