FEATURES:

- Material: Tin Plated CU UL listed for U.S. & Canada.
- Wire connector rated for 35Kv max.
 Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).
- Dimensions are for referene only.


L Series: L3048


POLARIS


PROGRAM: SOLIDWORKS
UPDATED: 4/2022

SALES REV: A

SIZE: B (11x17)







+			COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)									
			NSI			GREENLEE	ILSCO	BURNDY	T&B	HUSKIE		
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES	ILC-12/ILC-15 SERIES	Y-35, Y750, PAT 750	D, PAT 750 TBM-15, TBM-14M EP510C		10C
3/0AWG	1-7/16"	ORANGE	3/0AWG-#2AWG	KC12-3/0 (2)	CD10 (4)	HT41BA (4)	KC12-3/0 (2)	ILD-9 (4) KC12-3/0 (2)	U27RT (2)	15530 (4)	HT41BA (4)	CD10 (4)

