
FEATURES:

- 1.
- Material: Tin Plated CU UL listed for U.S. & Canada.
- 2. 3. 4.
- Wire connector rated for 35Kv max. Class B/C compressed, concentric, and compact copper conductor only.
- Expanded wire range when installed with dieless NSi compression 5. tool (N12ID).
- Dimensions are for reference only, tolerance is +/- .06". 6.

.82





+						PRESSION CONNECTOR TOOL AND DIE CHART (# OF CR				
I				NSI				GREENLEE		BUR
WIRE SIZE STRIP LENGTH		DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 5	SERIES	ILC-12/ILC-15 SERIES	Y-35. Y7 75
#3AWG	1-3/16"	WHITE	#3AWG-#6AWG	KC12-3 (2)	_	HT41AV (4)	KC12-3 (2)	ILD-3 (4)	KC12-3(2)	U3CF

nsiindus

MHITTE WHITTE WHITTE CLARR O'''''''''''''''''''''''''''''''''''										
1										
-1.10										
CRIMPS)										
BURNDY T&B HUSKIE	HUSKIE									
E Y750, PAT TBM-15, TBM-14M EP510C										
3CRT (2) – HT41AV (4) –										
stries.com/contactus 800.321.5847 🔊										

PROGRAM: SOLIDWORKS

SIZE: B (11x17)

UPDATED: 4/2022

SALES REV: A