
FEATURES:


- Material: Tin Plated CU UL listed for U.S. & Canada.
- Wire connector rated for 35Kv max.
 Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).
- Dimensions are for reference only, tolerance is +/- .06".




LN Series: L40N



PROGRAM: SOLIDWORKS
UPDATED: 4/2022 SALES REV: A
SIZE: B (11x17)





			COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)										
1			NSI			GREENLEE		ILSCO	BURNDY	T&B	HUSKIE		
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES		ILC-12/ILC-15 SERIES	Y-35. Y750, PAT 750	TBM-15, TBM-14M	EP510C	
4/0AWG	1-1/2"	PURPLE	4/0AWG-#1AWG	KC12-4/0 (2)	CD12 (4)	HT41BC (4)	KC12-4/0 (2)	ILD-10 (4)	KC12-4/0 (2)	U28RT (4)	15511 (4)	HT41BC (4)	CD12 (4)

