## **FEATURES:**

- Material: Tin Plated CU UL listed for U.S. & Canada.
- Wire connector rated for 35Kv max.
  Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).
- Dimensions are for reference only, tolerance is +/- .06".




## **LN Series: L4N**



PROGRAM: SOLIDWORKS
UPDATED: 4/2022

SALES REV: A
SIZE: B (11x17)





						COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)								
			NSI				GREENLEE		ILSCO	BURNDY	T&B	HUSKIE		
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES		ILC-12/ILC-15 SERIES	Y-35. Y750, PAT 750	TBM-15, TBM-14M	EP510C		
#4AWG	1-3/16"	GRAY	#4AWG-#6AWG	KC12-4 (2)	CD3 (4)	HT41AU (4)	KC12-4 (2)	ILD-3 (4)	KC12-4(2)	U4CRT (2)	15527-CK (4)	HT41AU (4)	CD3 (4)	

