
15 AMP NEMA L515 PLUG - BLACK BACK, WHITE FRONT BODY

PSL515P | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Plug 3wire 15amp 125v



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

SPECIFICATIONS

GENERAL INFO

Color: Black, White

Type: Plug

Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: 498

UL Standard: Yes
UN SPSC: 39121403

DIMENSIONS

Diameter (US): 1.516"
Length (US): 2.617"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: L515
Volts: 125V
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

