
30 AMP NEMA L530 FLANGED INLET, GRAY

L530FI | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Flanged Inlet, 3wire 30amp 125volt, Gray

- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Type: Flanged Inlet

Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

UR: No

DIMENSIONS

Depth (US): 1.750"

Diameter (US): 3.12"

TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L530

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



30 AMP NEMA L530 FLANGED INLET, GRAY

L530FI | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Flanged Inlet, 3wire 30amp 125volt, Gray

- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Type: Flanged Inlet

Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

UR: No

DIMENSIONS

Depth (US): 1.750"

Diameter (US): 3.12"

TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L530

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

