



### KT-LED54HID-EX39-850-D /G3

HID REPLACEMENT LED LAMP

#### **DESCRIPTION**

54W HID Replacement LED Lamp | 5000K | > 80 CRI | IP64 Rated















#### **PRODUCT FEATURES**

- Replacement for conventional metal halide lamp
- 50,000 + hour lifetime
- Environmentally friendly: No mercury used
- Instant startup
- UL listed
- DLC listed
- Operating temperature: -29°C/-20°F to 60°C/140°F
- Integral driver, eliminates the need for external driver or ballast; includes 4kV surge protection
- IP64 rated; integrated heat sink quickly dissipates heat and guides water intrusion out of the lamp
- Suitable for use in fully enclosed fixture
- Do not use with standard dimmers. Not compatible with phase dimmers. Dimming functions with sensors only

#### **OPERATING SPECIFICATIONS**

#### **ELECTRICAL CHARACTERISTICS**

Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	54W	>0.9	0.45A @ 120V 0.20A @ 277V

#### PHOTOMETRIC CHARACTERISTICS

Color Temperature (CCT)	5000K	
Luminous Flux*	8100 lm	
Color Rendering Index (CRI)	>80	
Efficacy	150 lm/W	
Visible Light Area	360⁰	
Efficacy	150 lm/W	

<sup>\*</sup> Based off of total lamp lumens

#### **SMART PORT**




On the top of the lamp is a low-voltage AUX port for lamp level sensor controls which are coming soon, Q2+ 2019.


#### **RATED LIFE**

**L70 (Hours)** 50,000

#### SPECTRAL DISTRIBUTION



#### **LUX DISTANCE CURVE**







# KT-LED54HID-EX39-850-D /G3 HID REPLACEMENT LED LAMP

#### **SMART PORT LED**



On the top of the lamp is a low-voltage AUX port for lamp level sensor controls.

#### **SMART PORT LED AUX SENSORS**



<sup>\*</sup> For use with continuous dimming applications.


#### WIRING INSTRUCTIONS

#### STEP 1

Disconnect power. Disconnect and remove existing ballast, capacitor, and/or ignitor (where applicable) from fixture.

#### STEP 2


Rewire for line voltage to the lamp socket.



# **O**AC 120-277\ Lamp holder NÒ


#### STEP 3


Install new LED replacement lamp. Ensure lamp is operating properly when power is turned on.





#### EX39-based lamps will work in both E39 and EX39 sockets.











## KT-LED54HID-EX39-850-D/G3

HID REPLACEMENT LED LAMP

#### PHYSICAL CHARACTERISTICS





#### **LAMP DIMENSIONS**

A (Illuminated Length)	5.07"	
B (Body Length)	9.80"	
C (Diameter)	3.34"	

BASE TYPE: EX39 (Mogul)

#### **ORDERING INFORMATION**

ORDER CODE	PACK QTY.	EASY CODE	UPC
KT-LED54HID-EX39-850-D/G3	12	QGT-69	843654123134

#### **CATALOG NUMBER BREAKDOWN**

KT-LED54HID-EX39-850-D/G3

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Type
- 5 Base Type
- 6 800 Series
- **7** Color Temperature
- 8 Direct-Drive Series
- 9 Generation