



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L600N 600 1/2" 2-Hole Long Barrel Compression Lug

Nsi Industries

Catalog Number	L600N
Manufacturer	Nsi Industries
Description	Compression Lug, 250 MCM Conductor Size, 600 MCM Conductor Size, Non-Insulated, Copper Conductor Material, Green Insulation Color, 2 Conductors, +90 °C Operating Temperature, 5.79 In Overall Length, 600 V Ac, 0.87 LB/Ea
Weight per unit	0.8700 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	600 MCM (STR)
Material	Copper
Number of Holes	2
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Green
Finish	Tin Plated

### Dimensions and Weight

Size	L=5.79 - W=1.72 - OD=1.19 - ID=.930
------	-------------------------------------

### Descriptions

Description	600 1/2" 2-HOLE LONG BARREL COMPRESSION LUG
extra long description	NSI L600N CU CMP Lug Long 600 MCM N
Features	2Hole Long Barrel Copper Compression Lug600 MCM-1/2" Bolt Long Barrel Copper Compression Lugs is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.

### Manufacturer Information

GTIN	00662381035189
UPC	662381035189

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - Two Hole



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight Per each	0.87

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Holes
standard	UL486A/B