

20 Amp NEMA Plug L620 -Black Back, White Front Body

L620P



Turnlok Plug 3wire 20amp 250v



features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

specifications

General Info

Color: Black, White

Type: Plug

Number Of Wires: 3

Listing Agencies/Third Party Information

CSA Standard: Yes CUL Listing No: No

cULus: Yes cURus: No

Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: 498 UL Standard: Yes UN SPS C: 39121403

UR: No

Dimensions

Depth U S: 2.20" Length U S: 2.57"

Technical Information

Amps: 20 Amp

NEMA Configuration Number: L620

Volts: 250V Volts A C: 250

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant