

Eaton L630C

Catalog Number: L630C

Eaton Arrow Hart ultra grip locking connector, #18-10 AWG, 30A, Industrial, 250V, Back wiring, Black, white, Ultra grip, L6-30, Two-pole, Three-wire, Nylon



General specifications

Product Name	Catalog Number
Eaton Arrow Hart standard locking connector	L630C
	UPC
	032664393600
Product Length/Depth	Product Height
1.92 in	3.93 in
Product Width	Product Weight
1.81 in	0.28 lb
Compliances	Certifications
RoHS Compliant	UL Listed
	NOM
	CSA certified

Product specifications

Special features

Watertight locking receptacle

Color

White

Black

Face/body material

Thermoplastic

Wiring method

Back

Material

Thermoplastic

Allowable wire size

#18-10 AWG

Amperage Rating

30A

Number Of Poles

Two-pole

Contact material

Brass

Type

Locking connector

Device grade

Commercial

NEMA configuration

L6-30

Design type

Standard locking connector

Number of wires

Grounding

3

Operating temperature

-20 to 60 °C (-4 to 140 °F)

Voltage rating

250 V

Cord diameter

0.25-0.69 in (6.4 mm-17.5 mm)

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - L630C](#)

Application

Industrial

Torque rating

20 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)