

# Specifications

## Eaton L630PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 250V, Back wiring, Yellow, Steel, Watertight, L6-30, Two-pole, Three-wire, Santoprene, 0.43 to 1.15 in, IP67

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart watertight locking plug
<b>CATALOG NUMBER</b>	L630PW
<b>UPC</b>	040893641799
<b>PRODUCT LENGTH/DEPTH</b>	6.78 in
<b>PRODUCT HEIGHT</b>	3.84 in
<b>PRODUCT WIDTH</b>	4.39 in
<b>PRODUCT WEIGHT</b>	1.025 lb
<b>COMPLIANCES</b>	RoHS Compliant Federal Specifications Classification W-C375
<b>CERTIFICATIONS</b>	CSA certified UL Listed NOM cULus Listed
<b>PRODUCT TYPE</b>	Watertight



Powering Business Worldwide

## Electrical Ratings

AMPERAGE RATING	30A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L6-30
NUMBER OF POLES	Two-pole
NUMBER OF WIRES	Grounding 3
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	250 V

## Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

## Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
DESIGN TYPE	Watertight locking plug
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Nylon
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight
TYPE	Locking plug

## Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 4
	NEMA 6P
	NEMA 6
	IP67
	NEMA 4X

## Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated brass

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - L630PW</a>
	<a href="#">Arrow Hart watertight locking plugs, connectors and receptacles spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

