## **FEATURES:**


- Material: Tin Plated CU UL listed for U.S. & Canada.
- Wire connector rated for 35Kv max.
  Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).
- Dimensions are for reference only, tolerance is +/- .06".


L Series: L638


**POLARIS** 

PROGRAM: SOLIDWORKS
UPDATED: 4/2022

SALES REV: A
SIZE: B (11x17)







+			COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)										
			NSI				GREENLEE		ILSCO	BURNDY	T&B	HUSKIE	
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES		ILC-12/ILC-15 SERIES	Y-35. Y750, PAT 750	TBM-15, TBM-14M	EP510C	
#6AWG	1-1/16"	BLUE	#6AWG-#8AWG	KC12-6 (2)	CD2 (4)	HT41GL (4)	KC12-6 (2)	ILD-2 (4)	KC12-6(2)	U5CRT (2)	15522 (4)	HT41GL (4)	CD2 (4)

