



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **L6N141 6AWG 1/4"STD 2H 5/8"SPC Cu CMP Lug**

*Nsi Industries*

Catalog Number	L6N141
Manufacturer	Nsi Industries
Description	2 Hole Long Barrel Copper Compression Lug 6 Awg - 1/4" Bolt - 5/8" Mounting Spacing Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. Allows Easy Inspection Of The Termination to Assure Complete Cable Insertion. Tin-Plated to Provide Corrosion and Low Contact Resistance. Marked With Die Index and Color Coded. Listed For 35KV Maximum When Properly Installed. Rated 600V. Culus 486A/B Listed. UL467 Listed On Sizes 6 Awg - 3/0 Awg. Temperature Rating 90 Degrees C.
Weight per unit	4.0 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Cable Size	# 6 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

### **Material, Color, and Finish**

Color	Blue
Finish	Tin Plated

### **Dimensions and Weight**

Size	L=2.36 - W=.420 - OD=.300 - ID=.200
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	6AWG 1/4"STD 2H 5/8"SPC CU CMP LUG
extra long description	NSI L6N-141 CU CMP Lug Long 6 AWG 1
Features	2 Hole Long Barrel Copper Compression Lug 6 AWG - 1/4" Bolt - 5/8" Mounting Spacing Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Long Description	2 Hole Long Barrel Copper Compression Lug 6 AWG - 1/4" Bolt - 5/8" Mounting Spacing Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Product Type	Cu CMP Lug Long 6 Awg 1/4 Bolt 5/8 Spac
Special Features	# 6 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing

## Manufacturer Information

Brand	NSi
GTIN	00662381339003
Manufacturers Part Number	L6N-141
UPC	662381339003

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - Two Hole

## Packaging

Carton	1
Weight Per each	4

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)