



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106



L7T824GC850DX2 *Delisted* 7W Led T8 24" 50K Line DBL/SNGL Ended *Keystone Technologies*

Catalog Number	L7T824GC850DX2
Manufacturer	Keystone Technologies
Description	7W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 2, 5000K, Direct Drive, Single or Double Ended
Weight per unit	0.4000 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	950
Nominal Length	24 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	7
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Description	7W LED T8 24" 50K LINE DBL/SNGL ENDED
extra long description	Key KT-LED7T8-24GC-850-DX2-CP 7W LE
Long Description	7W LED T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 2, 5000K, Direct Drive, Single or Double Ended
Product Type	7W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input,



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106

Manufacturer Information

Brand	Keystone
GTIN	00890949016398
Manufacturers Part Number	KT-LED7T8-24GC-850-DX2-CP
UPC	890949016398

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Availability

Status	Inactive
--------	----------

Packaging

Carton	25
Weight Per each	0.4

Uses, Certifications, and Standards

Energy Star	Y
-------------	---