



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L81200C 8" Black Cable Tie

Abb Installation Products, Inc

Catalog Number	L81200C
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Black Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius 1850 F), Weather and Ultraviolet Resistant For Indoor and Outdoor Applications, Length Of 200MM (7.87 Inches), Width Of 7.6MM (0.30 Inches), Thickness Of 1.6MM (0.06 Inches), Tensile Strength Rating Of 534 Newtons (120 Pounds)
Weight per unit	0.0080 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Bundle Diameter	0.28 to 1.97 in , 7 to 50 mm
Material	Nylon/Polyamide 6.6 Weather Resistant
Tensile Strength	120 pounds , 534 newtons

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	8.35 in , 212 mm
Thickness	0.08 in , 2 mm
Width	0.3 in , 7.6 mm

Descriptions

Description	8" BLACK CABLE TIE
extra long description	ABB L-8-120-0-C UV NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius 1850 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 200mm (7.87 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.6mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)
Product Type	Uv Nylon

Manufacturer Information

Brand	Catamount
GTIN	00728494917405
Manufacturers Part Number	L-8-120-0-C
UPC	728494917405

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HEAVY DUTY



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
--------	-----

Package	5000
---------	------

Weight Per each	0.008
-----------------	-------

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------