

## 20 Amp NEMA L820 Single Receptacle

L820R



Industrial Spec Grade SingleTurnlok  
20amp 480V Receptacle



### features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### specifications

#### General Info

Type: Single, Receptacles

#### Listing Agencies/Third Party Information

CSA Standard: Yes  
CUL Listing No: No  
cURus: No  
Federal Spec: No  
UL Listing No: 498  
UL Standard: Yes

UN SPS C: 39121403

UR: No

**Dimensions**

Depth U S: 1.19"

Height U S: 3.28"

Width U S: 1.61"

**Technical Information**

Amps: 20 Amp

NEMA Configuration Number: L820

**Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant