



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LA199850EC0D61 8/80PK 9W(60) A19 Eco Dimmable 5000K Mol=4.35

*Topaz Electric, Use 751338*

Catalog Number	LA199850EC0D61
Manufacturer	Topaz Electric, Use 751338
Description	Led A-Shape Eco Lamps 9W - 5000K
Weight per unit	N/A
Product Category	Led A-Line A Shape Lamps

### Features

average life	Topaz
Base	E26
beam angle	230
Equivalent Wattage	60
Fixture Type	Enclosed Luminaires
Lamp Type	LED
load	Topaz
lumens	Topaz
Shape	A19
Voltage Rating	120
Warranty	5
Wattage	9

### Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	5000
Lens Material	Plastic

### Dimensions and Weight

Size	2.4 IN (Dia.) x 4.4 IN
------	------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	8/80PK 9W(60) A19 ECO DIMMABLE 5000K MOL=4.35
extra long description	TopazUPC LA19/9/850/ECO/D-61 8/80PK
Features	Our ECO style A19 lamps offers a 230 beam angle suitable for all general lighting applications, and are a low cost-of-use alternative to traditional incandescent lamps. LED A-Shape lamps are ideal for both residential and commercial settings including down lights, wall sconces, ceiling fans, table and floor lamps. Dimmable down to 10% for additional energy savings and ambiance control.
Long Description	LED A-Shape ECO Lamps 9W - 5000K
Product Type	8/80PK 9W(60) A19 Eco Dimmable 5000K Mol=4.35"
Special Features	Features: 85 Energy Savings Compared to 60W Incandescent, Long Life Upto 10X Longer than Traditional Incandescents, Mercury Free

## Manufacturer Information

Brand	Topaz Lighting Corp.
GTIN	00751338005372
Manufacturers Part Number	LA19/9/850/ECO/D-61
UPC	751338005372

## Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	LED A-Shape ECO Lamp

## Packaging

Carton	1
Package Type	CASE
Weight Per each	0

## Uses, Certifications, and Standards

Application	Topaz
Mounting	Fixture Mount
Operating Temperature	-4 to +104
standard	RoHS Compliant, cULus Listed