

# Eaton BUSH915

Catalog Number: BUSH915

Eaton Crouse-Hinds series CGB cable gland bushing, Neoprene, 80°C, 1-1/4", 1-1/2", 2" or 2-1/2" NPT

## General specifications

|   |                |
|---|----------------|
| Product Name                                      | Catalog Number |
| Eaton Crouse-Hinds series CGB cable gland bushing | BUSH915        |
|   | UPC            |
|   | 782274111407   |
| Product Length/Depth                              | Product Height |
| 0.001 in  | 0.001 in       |
| Product Width                                     | Product Weight |
| 0.001 in  | 0.07 lb        |

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

## Product specifications

### Thread Size

1-1/4", 1-1/2", 2" or 2-1/2"

### Thread type

NPT

### Material

Neoprene

### Special features

80°C

## Resources

### Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

### Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

### Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

### Installation instructions

[IF 513A - CG Fittings Installation](#)

### Specifications and datasheets

[Eaton Specification Sheet - BUSH915](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)