



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



LCCX814AFL #8AWG, 1/4STD 2H, 5/8"SPC 90D LNG BRL CMP Lug *Panduit Corporation*

Catalog Number	LCCX814AFL
Manufacturer	Panduit Corporation
Description	Two-Hole, Flex Lug, Long Barrel, #8 Awg Wire, 1/4 Stud Hole, .63 Hole Spacing, 90° Angle Tongue.
Weight per unit	0.0230 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Tin-Plated Copper
media	Yes
Number of Holes	2
Stud Size	1/4

Material, Color, and Finish

Color	Red
-------	-----

Dimensions and Weight

Size	#8 AWG Class B, C, G, H, I, K, M and DLO
------	--

Descriptions

Description	#8AWG,1/4STD 2H,5/8"SPC 90D LNG BRL CMP LUG
extra long description	PAN LCCX8-14AF-L Pan-Lug™ LCCX8-14A
Long Description	Two-hole, flex lug, long barrel, #8 AWG wire, 1/4 stud hole, .63 hole spacing, 90° angle tongue.
Product Type	Pan-Lug™ LCCX8-14AF-L Compression Connectors - Lugs
Special Features	Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V

Manufacturer Information

Brand	PANDUIT
GTIN	00074983425280
Manufacturers Part Number	LCCX8-14AF-L
UPC	074983425280

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Compression Lug

Packaging

Carton	1
Package	50
Weight Per each	0.023



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Uses, Certifications, and Standards

Mounting
standard

3/4

CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File
#E52164, ABS approved