



HALO[®]

LCR Light Commercial Retrofit

Solutions for Mixed-Use and
Light Commercial Spaces



Product Features



- Direct Mount 2", 4", 6" & 8" downlights
- Field Selectable 2700 / 3000 / 3500 / 4000 / 5000 K CCT; 90+ CRI
- Up to 8000lm (8"), Up to 3000lm (6"), Up to 1200lm (4"), 800lm (2")
- Wet location listed, suitable for shower applications
- Remote driver / junction box, 120-277V, 5% 0-10V dimming
- Held securely in 0.5" – 1.25" thick ceilings with retention springs
- Airtight and suitable for direct contact with insulation

The **LCR** is an LED downlight family with a remote driver / junction box positioned as HALO's light commercial solution for new construction and remodel applications.

Value Proposition

- No housing required, reduces installation time and expense
- Wide distribution patterns are ideal for general area illumination
- High powered direct mounts with high CRI and efficiency
- Regressed lens provides high optical cutoff and improves visual comfort
- Residential, Office, Hospitality and Healthcare verticals



LCR2
2-inch
800 lumens



LCR4
4-inch
800 lumens | 1200 lumens



LCR6
6-inch
1500 lumens | 2100 lumens | 3000 lumens



LCR8
8-inch
3000 lumens | 5000 lumens | 8000 lumens

Catalog Number	Material Number	Description	UPC	Accessories			
				Mounting Frame	Designer Trims	Oversized Trim	Extension Cable
LCR2089FSE010MW	13261013	2.5" 800 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083889969		•		•
LCR2089FS1EMW	13393464	2.5" 800 lumen, LCR Direct Mount, Round, 120V	080083130061		•		•
LCR4089FSE010MW	13261014	4" 800 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083889983	•	•	•	•
LCR4129FSE010MW	13261015	4" 1200 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083890002	•	•	•	•
LCR6159FSE010MW	13261016	6" 1500 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083890026	•	•	•	•
LCR6219FSE010MW	13261017	6" 2100 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083890040	•	•	•	•
LCR6309FSE010MW	13261018	6" 3000 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083890064	•	•	•	•
LCR8309FSE010MW	13261019	8" 3000 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083890088	•	•	•	•
LCR8509FSE010MW	13261140	8" 5000 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083890101	•	•	•	•
LCR8809FSE010MW	13261141	8" 8000 lumen, LCR Direct Mount, Round, 120-277V, 0-10V	080083890125	•	•	•	•



mounting frame



designer trims



oversized trim ring



extension cable