



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353



## LD12T5H024GC835D \*Delisted\* 12W 120-277V 35K Led T5 *Keystone Technologies*

Catalog Number	LD12T5H024GC835D
Manufacturer	Keystone Technologies
Description	12W Led T5 Tube, Shatter-Proof Coated Glass, Internal Driver, 2 FT., 3500K, 120-277V Input
Weight per unit	0.2800 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1500
Nominal Length	24 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12
Wire Type	N/A

### Material, Color, and Finish

Base Type	G5
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

### Descriptions

Description	12W 120-277V 35K LED T5
extra long description	Key KT-LED12T5HO-24GC-835-D-CP 12W
Long Description	12W LED T5 Tube, Shatter-Proof coated Glass, Internal Driver, 2 ft., 3500K, 120-277V Input
Product Type	12W Led T5 Tube, Shatter-Proof Coated Glass, Internal Driver

### Manufacturer Information

Brand	Keystone
GTIN	00890949016060
Manufacturers Part Number	KT-LED12T5HO-24GC-835-D-CP
UPC	890949016060



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
--------	----

Weight Per each	0.28
-----------------	------

## Uses, Certifications, and Standards

Energy Star	Y
-------------	---