



ESSENTIAL SERIES

GENERAL PURPOSE LED BULBS

KT-LED11A19-O-8XX

REPLACEMENT LAMP

DESCRIPTION

11W A19 Lamp | 2700–5000K | >90 CRI |
Omni-Directional



LAMP TYPE: A19

BASE TYPE: E26 (Medium)

WATTAGE: 11W

COLOR TEMPERATURE: 2700–5000K

COLOR RENDERING INDEX (CRI): >80

WARRANTY: 3 Years

RATED LIFE: L70 (15,000 Hours)

TYPICAL APPLICATIONS

- Table, desk, and floor lamps
- Wall sconces
- Surface-mount ceiling fixtures
- General lighting
- Pendant lights

PRODUCT FEATURES

- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- Smooth, uniform dimming
- Suitable for use in damp locations
- UL enclosed rated, suitable for use in totally enclosed luminaires
- Operating temperature range –4°F/–20°C to 95°F/35°C
- PF >0.70
- ANSI compliant construction ensures fitment for intended applications
- Meets Energy Star requirements
- UL Listed
- Complies with Part 15 of FCC


ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED11A19-O-827	A19 bulb; Omni-directional; Dimmable	2700K	120V	11W	75W halogen	E26	1100 lm	>80	230°	Yes	100 lm/W
KT-LED11A19-O-830	A19 bulb; Omni-directional; Dimmable	3000K	120V	11W	75W halogen	E26	1100 lm	>80	230°	Yes	100 lm/W
KT-LED11A19-O-840	A19 bulb; Omni-directional; Dimmable	4000K	120V	11W	75W halogen	E26	1100 lm	>80	230°	Yes	100 lm/W
KT-LED11A19-O-850	A19 bulb; Omni-directional; Dimmable	5000K	120V	11W	75W halogen	E26	1100 lm	>80	230°	Yes	100 lm/W

KT-LED11A19-O-8XX

REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



LAMP DIMENSIONS

A (Diameter)	2.36"
B (Length)	4.43"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	15.55" × 13.07" × 10"
Carton Weight	10.6 lbs

ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	EASY CODE	UPC
KT-LED11A19-O-827	60 pcs	UQF-21	843654126579
KT-LED11A19-O-830	60 pcs	ERC-16	843654126586
KT-LED11A19-O-840	60 pcs	KBO-93	843654127545
KT-LED11A19-O-850	60 pcs	QXQ-10	843654126593

CATALOG NUMBER BREAKDOWN

KT-LED11A19-O-8XX

1 2 3 4 5 6 7

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 800 Series
- 7 Color Temperature