



GE  
Lighting

### 65137 - GE LED PAR30

LED12DP30S827/20

 Energy-efficient LED lamps. Long life.

### Product Photo



### GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26
Bulb Shape	PAR30

### PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	4400 cd
Lumens per Watt (Efficacy)	62 lm
Nominal Initial Lumen per Watt	62
Rated Beam Spread	20 deg
Initial Lumens-nominal	740 lm
Color Rendering Index-CRI	83
Color Temperature	2700 K

### PRODUCT INFORMATION

Product Code	65137
Description	LED12DP30S827/20
Alternative Unit Of Measure	CASE

### ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	12 W