




GE
Lighting

90150 - GE LED PAR38

LED12DP382W83025

 Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor and outdoor Floodlight
Rated Life (Hours)	25000 h
Bulb Shape	PAR38

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	4400 cd
Lumens per Watt (Efficacy)	79.2 lm
Nominal Initial Lumen per Watt	79
Rated Beam Spread	25 rad
Initial Lumens-nominal	950 lm
Color Rendering Index-CRI	84
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	90150
Description	LED12DP382W83025
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	12 W