

Product Number: 79528

Order Abbreviation: LED12T8/L48/FG/841/SUB/G6

General Description: 4ft SubstiTUBE LED T8, frosted glass, 12W, 82CRI, 1650 Lumen, 4100K, 50000 life



Product Information

Life Time (L70)	50000
Dimming	No
Abbrev. With Packaging Info.	LED12T8L48FG841SUBG6 10/CS 1/SKU
Average Rated Life (hr)	50000
Bulb	T8
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	4100
Color Rendering Index (CRI)	82
Lumens	1650
Approx. Lumens	1650
Nominal Voltage (V)	120.00
Nominal Wattage (W)	12.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED12T8/L48/FG/841/SUB/G6
UPC Code	UPC046135795282
Lamp Finish	Frosted

Product Number: 79528

Order Abbreviation: LED12T8/L48/FG/841/SUB/G6

General Description: 4ft SubstiTUBE LED T8, frosted glass, 12W, 82CRI, 1650 Lumen, 4100K, 50000 life



Product Information

Life Time (L70)	50000
Dimming	No
Abbrev. With Packaging Info.	LED12T8L48FG841SUBG6 10/CS 1/SKU
Average Rated Life (hr)	50000
Bulb	T8
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	4100
Color Rendering Index (CRI)	82
Lumens	1650
Approx. Lumens	1650
Nominal Voltage (V)	120.00
Nominal Wattage (W)	12.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED12T8/L48/FG/841/SUB/G6
UPC Code	UPC046135795282
Lamp Finish	Frosted